

## New DuraStack Half and Full Angle Rings

DuraVent has added a new Half and Full Angle Ring to the DuraStack product line. The new half and full angle rings are used to support and guide the stack.

### Applications

- Half Angle Rings are used as saddle supports in horizontal and sloped runs.
- Full Angle Rings are used as guides for vertical runs of pipe to maintain alignment and provide lateral support while still permitting vertical expansion.

### Construction

The inside diameter is 1/8" larger than the outer diameters of the stack, allowing movement of the stack within the ring. Full Angle Rings include hardware to assemble the two halves together. Please refer to installation instructions for appropriate spacing.

### Features

- Manufactured with stainless steel
- Available in standard lead time

ORDER #	Description	ORDER #	Description
DIS5HARP	Half Angle Ring DIS 5"	DIS5FARP	Full Angle Ring DIS 5"
DIS6HARP	Half Angle Ring DIS 6"	DIS6FARP	Full Angle Ring DIS 6"
DIS8HARP	Half Angle Ring DIS 8"	DIS8FARP	Full Angle Ring DIS 8"
DIS10HARP	Half Angle Ring DIS 10"	DIS10FARP	Full Angle Ring DIS 10"
DIS12HARP	Half Angle Ring DIS 12"	DIS12FARP	Full Angle Ring DIS 12"
DIS14HARP	Half Angle Ring DIS 14"	DIS14FARP	Full Angle Ring DIS 14"
DIS16HARP	Half Angle Ring DIS 16"	DIS16FARP	Full Angle Ring DIS 16"
DIS18HARP	Half Angle Ring DIS 18"	DIS18FARP	Full Angle Ring DIS 18"
DIS20HARP	Half Angle Ring DIS 20"	DIS20FARP	Full Angle Ring DIS 20"
DIS22HARP	Half Angle Ring DIS 22"	DIS22FARP	Full Angle Ring DIS 22"
DIS24HARP	Half Angle Ring DIS 24"	DIS24FARP	Full Angle Ring DIS 24"
DIS26HARP	Half Angle Ring DIS 26"	DIS26FARP	Full Angle Ring DIS 26"
DIS28HARP	Half Angle Ring DIS 28"	DIS28FARP	Full Angle Ring DIS 28"
DIS30HARP	Half Angle Ring DIS 30"	DIS30FARP	Full Angle Ring DIS 30"
DIS32HARP	Half Angle Ring DIS 32"	DIS32FARP	Full Angle Ring DIS 32"
DIS34HARP	Half Angle Ring DIS 34"	DIS34FARP	Full Angle Ring DIS 34"
DIS36HARP	Half Angle Ring DIS 36"	DIS36FARP	Full Angle Ring DIS 36"



HALF ANGLE RING



FULL ANGLE RING

Note: Within DuraQuote, the cradle supports will be replaced by the new half ring. For vertical sections, two half rings (full ring) can be installed together.